

PSEN sl-1.0fm 2.1 1actuator

570623



Actuator (free-moving), fully coded, for safety locking device PSENslock, aluminium base plate, for holding force 1000 N Important information: This item is at the end of the product lifecycle and therefore will no longer be available in the foreseeable future. Please get in touch with your PILZ contact to find a suitable alternative or successor product.

Technical details

General data	
Approval:	CE, UKCA, cULus Listed, FCC, IC, TÜV, EAC (Eurasian)
Sensor principle:	Transponder
Coding level to ISO 14119:	hoch
Transponder coding:	vollcodiert
unit type:	Betätiger
Technical data	
Environmental data	
Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	-25
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. F. bei 40 °C
EMC to standard ...:	EN 55011: class A, EN 60947-5-3, EN 62061
Vibration to standard ...:	EN 60947-5-2
Acc. shock to standard1:	30g
Acc. shock to standard2:	10g
Protection type, housing:	IP67
Mechanical data	
Housing material upper part:	PBT

Material of anchor plate:	Stahl vernickelt
Material actuator:	Anticorodal, hart eloxiert
Height dimension:	188
Width dimension:	52
Depth dimension:	22
Net weight:	590
Gross weight:	670
Environment	
WEEE klassifikation (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85389099
UNSPSC 25:	39122205
EAN-Code:	4046548073959
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272606
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001487
Volume:	0 dm3

Optional accessories



540312

PSEN screw M5x20 10pcs



570550

PSEN sl bracket swing door



570551

PSEN sl bracket sliding door
