

PNOZ s11 C 24VDC 8 n/o 1 n/c

751111



PNOZsigma contact expansion, outputs: 8 N/O, 1 N/C, UB = 24 V DC, width: 45 mm, plug-in spring-loaded terminals, contact block for contact expansion in connection with safety-related control components.

Technical details

General data	
Approval:	CCC, CE, UKCA, cULus Listed, KOSHA, TÜV, EAC (Eurasian)
Technical data	
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	7a, 7c I
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead, Lead oxide
%-part of the pollutant:	> 0,1%
CAS No.:	7439-92-1, 1317-36-8
SCIP entry available:	yes
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27371819
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000019
ETIM Reference Feature:	EC001449

UNSPSC 25:	39122331
GTIN:	4046548050318
Volume:	0.792 dm3
Harmonized System Code:	85364900
Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1

Optional accessories

751012

PNOZ s Set2spring loaded terminals 45mm



750020

PNOZ s connector (10 pieces)