

PNOZ msi b1 Box 15p

773880



Adapter box for speed monitoring module, PNOZmulti Classic, 3 x 15- pin D-Sub connector, 2 x socket, 1 x connector, can be clipped to top hat rails.

Technical details

General data	
Approval:	CE, UKCA
Technical data	
Environmental data	
Ambient temperature:	0 - 60 °C
Condensation permitted?:	Not permitted
Mechanical data	
Connector type 1:	15-pin D-Sub female connector
Connector type 2:	15-pin D-Sub female connector
Connector type 3:	15-pin D-Sub male connector
Housing material connector 3:	PBT
Contact surfaces material 1:	Au
Material of pins:	Brass
Material of sockets:	Brass
Approvals for connector 1:	UL94 V-0
Approvals for connector 2:	UL94 V-0
Approvals for connector 3:	UL94 V-0
Housing material:	Hot dip galvanised steel
Height dimension:	60 mm
Width dimension:	66 mm

Depth dimension:	30 mm
Net weight:	134 g
Gross weight:	145 g
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	6c
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1
WEEE classification (08/2018):	5 devices (feed size < 50cm)
SCIP entry available:	0
Commercial data	
Harmonized System Code:	85444290
UNSPSC 25:	39122205
EAN-Code:	4046548044614
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27440108
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002585
Volume:	0 dm3