

PNOZ msi b0 cable 15/RJ45

773881



Cable with 15-pin, D-Sub connector for adapter box PNOZ msi b1 (773880), cable length 0.3 m.

Technical details

General data	
Approval:	CE, UKCA
Technical data	
Environmental data	
Ambient temperature:	0 - 60 °C
Condensation permitted?:	Not permitted
Mechanical data	
Connector type 1:	15-pin D-Sub male connector
Shape of connector type 1:	straight
Connector type 2:	8-pin RJ45 male connector
Shape of connector type 2:	straight
Contact surfaces material 1:	Au
Contact surfaces material 2:	Au
Material of pins:	Brass
Material of sockets:	Brass
Cable material K1:	Cu
Cable type K1:	Li9YC11Y
Length cable:	0.3 m
Tolerance of cable length K1:	+ 0.035m
Colour cable insulation 1:	Green, similar to RAL6018

Housing colour:	Silver
Material of cable insulation 1:	PUR
Trailing capability of cable 1:	yes
Bend radius (when laying) K1:	8 x Ø
Max. outside diameter cable K1:	6 - 6 mm
Conductor cross section:	0.14 - 0.14 mm ²
Shielding K1:	yes
Number of conductors:	8
Approvals for cable K1:	UL AWM-Style 20233
Approvals for connector 1:	UL94 V-0
Approvals for connector 2:	UL94 V-0
Housing material:	PC+ABS
Height dimension:	32 mm
Width dimension:	40 mm
Depth dimension:	16 mm
Net weight:	38 g
Gross weight:	48 g
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	6c
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1
WEEE classification (08/2018):	5 devices (feed size < 50cm)
SCIP entry available:	0
Commercial data	

Harmonized System Code:	85444290
UNSPSC 25:	26121603
EAN-Code:	4046548044621
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27060313
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001855
Volume:	0 dm3