

PNOZ mli1p 10m screw

773891



Cable for safe connection of 2 PNOZ ml1p, 5-pin shielded, plug-in screw terminals, 10 m.

Technical details

General data

Approval: cULus Listed

Technical data

Mechanical data

Connector type 1: 5-pin female connector

Connector type 2: 5-pin female connector

Contact surfaces material 1: Tin-plated

Material of sockets: Cu alloy

Length cable: 10 m

Colour cable insulation 1: Grey

Housing colour: Black RAL 9011

Trailing capability of cable 1: no

Shielding K1: yes

Number of conductors: 5

Approvals for connector 1: UL94 V-0

Approvals for connector 2: UL94 V-0

Height dimension: 22.6 mm

Width dimension: 17.5 mm

Depth dimension: 11.6 mm

Net weight: 273 g

Gross weight:	292 g
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	6c
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1
WEEE klassifikation (08/2018):	5 devices (feed size < 50cm)
SCIP entry available:	0
Commercial data	
Harmonized System Code:	85444290
UNSPSC 25:	26121603
EAN-Code:	4046548050332
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27060313
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001855
Volume:	0 dm3