

PNOZ XV3P C 30/24 VDC 3n/o 2n/o t

787510



Safety relay (standalone), inputs: 1/2-channel wiring with/without detection of shorts across contacts, outputs: 3 N/O, 2 N/Ot-d (t = 0.1 - 30 s), automatic/monitored start, UB = 24 V DC, width: 45 mm, plug-in spring-loaded terminals, monitoring of E-STOP, safety gates.

Technical details

General data

Approval: CCC, CE, UKCA, cULus Listed, TÜV, EAC (Eurasian)

Technical data

Environment

RoHS directive: 2011/65/EU, 2015/863/EU

RoHS conformity: yes

RoHS exceptions: yes

RoHS except.s acc. to direct.: 7a, 7c I

REACH compliance: contains min. 1 SVHC-substance

REACH included substances: Lead, Lead oxide

%-part of the pollutant: > 0,1

CAS No.: 7439-92-1, 1317-36-8

SCIP entry available: yes

WEEE classification (08/2018): 5 devices (feed size < 50cm)

Commercial data

ECLASS version: ECLASS-13

ECLASS Reference Feature: 27371819

ETIM Version: ETIM-9.0

ETIM Reference Group: EG000019

ETIM Reference Feature: EC001449

UNSPSC 25:	39122331
GTIN:	4046548008265
Volume:	0.605 dm3
Harmonized System Code:	85364900
Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1

Optional accessories

374291

PNOZ X Set spring loaded terminals P3+P4

