

PMC Expansion Card Profibus DP Slave

8176280



Card can be used in PM Ctendo DD5 & PMCprotego.

Technical details

General data	
Approval:	CE, UKCA
Technical data	
PROFIBUS-DP interface	
Profibus type:	Slave
Perm. PROFIB. statn. addresses:	1 ... 127d
Setting PROFIBUS station addr.:	Software
Connector type Profibus inter.:	9-pin D-Sub female connector
Name PROFIBUS protocol:	PPO Type 2
PROFIBUS operating modes:	AutoBaud
Name description file profib:	prt_045d.gsd
PROFIBUS manufacturer ID:	045Dh
Environmental data	
Ambient temperature:	0 - 40 °C
Mechanical data	
Housing material front plate:	Aluminium
Net weight:	90 g
Gross weight:	340 g
Environment	
RoHS conformity:	yes

REACH compliance:	Contains no SVHC substances
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27023191
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC002025
UNSPSC 25:	39121021
GTIN:	4046548057935
Volume:	2.708 dm3
Harmonized System Code:	85439000
Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1