

## Brake resistor 600W/33R/T/U

8176372

suitable for the PMCprotego D/01-12A and PM Ctendo DD4/01-20A Type: FZECQU 400 x 65-33 Performance at 40° C/100 % ED: 600 W Resistance value: 33 OHM Temperature switch 180° C: Signal contact 2A/24 V DC (DC11) UL version.



## Technical details

General data	
Approval:	CE
Technical data	
Mechanical data	
Net weight:	3000 g
Gross weight:	3500 g
Environment	
RoHS conformity:	yes
REACH compliance:	Contains no SVHC substances
WEEE classification (08/2018):	0 not relevant
Commercial data	
Harmonized System Code:	85333900
UNSPSC 25:	39121021
EAN-Code:	4046548059250
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27023291
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC002025
Volume:	0 dm3