

PMCcable FD/D4B8/020/Q25/S1

8177274



Feedback cable for EnDat 2.2; Cable assembled on both sides Sub-D15 connector <> con.15 round connector 12-pin SpringTec; suitable for all PMC servo controllers (DD5, protego) and the motors PM Ctendo SZ.3x; Length 20m.

Technical details

Technical data

Environmental data

Ambient temperature: -20 - 80 °C

Mechanical data

Connector type 1: P 12-pin M15 female connector

Shape of connector type 1: straight

Connector type 2: 15-pin D-Sub male connector

Shape of connector type 2: straight

Contact surfaces material 1: Au

Contact surfaces material 2: Au

Length cable: 20 m

Material shield surface K1: Sn

Colour cable insulation 1: Green

Material of cable insulation 1: PUR

Trailing capability of cable 1: yes

Max. outside diameter cable K1: 7.2 - 7.8 mm

Cross section data cable K1: (4 x 2 x 0.25) mm²

Shielding K1: yes

Type of shielding K1: Wire mesh

Net weight: 1700 g

Gross weight:	1960 g
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85444290
UNSPSC 25:	26121603
EAN-Code:	4046548086270
ECLASS version:	ECLASS-13
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001855