

PRCM1

9C000001



Roboter Control Module; Cabinet complete: Safety Controller, PSS4000; CNC, PMCprimo MC; Robotic FS-function blocks

Technical details

General data

Approval: BG

Technical data

Electrical data

Supply voltage (V): 100 - 240 V

Type of supply voltage U1: AC

Device circuit breaker U1: Max. 16 A

Connection cross section: 3x1.5 mm²

Environmental data

Ambient temperature: 0 - 35 °C

Perm. operating height ASL: 2000 m

Protection type standard: EN 60529

Mechanical data

Cable entry: Inlets, outlets below

Design: Standing cabinet

Width dimension: 500 mm

Depth dimension: 300 mm

Net weight: 31000 g

Gross weight: 34140 g