

PIT gb key button

G1000007

PITgatebox key switch 1x40°, spring-return, (spare part). Mounting hole: 22.3mm



Technical details

| | |
|--------------------------------|------------------------------|
| General data | |
| Approval: | cURus, TÜV |
| Technical data | |
| Environmental data | |
| Ambient temperature: | -25 - 70 °C |
| Mechanical data | |
| Width dimension: | 29.8 mm |
| Depth dimension: | 29.8 mm |
| Net weight: | 40 g |
| Gross weight: | 42 g |
| Environment | |
| RoHS directive: | 2011/65/EU, 2015/863/EU |
| RoHS conformity: | yes |
| RoHS exceptions: | no |
| REACH compliance: | Contains no SVHC substances |
| WEEE classification (08/2018): | 5 devices (feed size < 50cm) |
| Commercial data | |
| ECLASS version: | ECLASS-13 |
| ECLASS Reference Feature: | 27371291 |
| ETIM Version: | ETIM-9.0 |

| | |
|-------------------------------|------------------|
| ETIM Reference Group: | EG000017 |
| ETIM Reference Feature: | EC002024 |
| UNSPSC 25: | 39122205 |
| GTIN: | 4046548089608 |
| Volume: | 0 dm3 |
| Harmonized System Code: | 85365080 |
| Type of tariff number: | TARIC |
| Use of customs tariff number: | Ausfuhr, Einfuhr |
| Quantity per packaging unit: | 1 |