

## PIT gb DLLE y

G1000033



PITgatebox (pushbutton unit), housing with E-STOP with signal contact(2 NC), 2 illuminated pushbuttons (per 1 NO), 1 non-illuminated pushbutton (1 NO), 12-pin M12 male connector, incl. colour cap set

## Technical details

### General data

Approval:	CE, UL/cUL, UKCA, EAC (Eurasian)
Self-monitored:	no
Lamp:	LED
Lamp colour:	white

### Technical data

#### Electrical data

Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	DC
Power consumption DC:	12 W
Min. contact current:	1 mA

#### Emergency stop

Number, E-STOP N/C:	2
Number, E-STOP signal contact:	1
Release type emergency stop:	Turn release
Switch cap. E-STOP to standard:	EN 60947-5-1
Contact material E-STOP:	Ag
Cont. mat. sign. cont. E-STOP:	Au

#### Push button

Number, pushbutton:	3
---------------------	---

Number of pushbutton N/O:	3
Switch cap. p/b to standard:	EN 60947-5-1
Contact material pushbutton:	Ag
<b>Environmental data</b>	
Ambient temperature:	-20 - 60 °C
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
Vibration to standard ...:	EN 60947-5-2
Acc. shock to standard1:	30g
Clearance & creepage dist. to:	EN 60947-1
Overvoltage category:	III
Pollution degree clear.&creep.:	3
UL enclosure type:	type 1
<b>Mechanical data</b>	
Mounting position:	any
Connection type:	M12, 12-pin male
Housing material:	Zn
Height dimension:	293 mm
Width dimension:	40 mm
Depth dimension:	40 mm
Net weight:	800 g
Gross weight:	1200 g
<b>Environment</b>	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
<b>Commercial data</b>	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27371216
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017

ETIM Reference Feature:	EC000225
UNSPSC 25:	39122205
GTIN:	4046548097931
Volume:	0 dm3
Harmonized System Code:	85365019
Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1

## Obligatory accessories



570356

PSEN cable M12-12sf 50m



570354

PSEN cable M12-12sf 20m



570355

PSEN cable M12-12sf 30m



570352

PSEN cable M12-12sf 5m



570353

PSEN cable M12-12sf 10m



570350

PSEN cable M12-12sf 2m



570351

PSEN cable M12-12sf 3m

## Optional accessories



G1000010

PIT gb blind cover



G1000012

PIT gb fixing spanner



G1000013

PIT gb color cover wh s1



G1000014

PIT gb color cover wh s2



G1000015

PIT gb color cover wh s3



G1000016

PIT gb color cover wh s4



G1000017

PIT gb color cover bl s5

G1000018

PIT gb color cover bl s6



---

G1000019

PIT gb color cover bl s4



---

G1000009

PIT gb color covers

