

KUNBUS-GW Profibus

Z9000008



Modular gateway PROFIBUS, communication module for the base module RevPi Core / RevPi Core 3, a max. of two different communication modules can be connected, housing dimensions (H x W x D): 96 x 22.5 x 110.5 mm, protection type: IP 20, connection to the fieldbus: D-SUB 9 female, device function: Slave, max. data length input data: 244 Byte, max. data length output data: 244 Byte.

Technical details

General data

Approval: CE, UKCA

Technical data

Mechanical data

Height dimension: 96 mm

Width dimension: 22.5 mm

Depth dimension: 110.4 mm

Net weight: 89 g

Gross weight: 98 g

Environment

WEEE classification (08/2018): 5 devices (feed size < 50cm)

Commercial data

Harmonized System Code: 85389091

UNSPSC 25: 39122331

EAN-Code: 4046548093216

ECLASS version: ECLASS-13

ECLASS Reference Feature: 27242290

ETIM Version: ETIM-9.0

ETIM Reference Group: EG000024

ETIM Reference Feature: EC001423

Volume:

0 dm³

Obligatory accessories



Z9000016

GW Connector for Modular Gateways