

KUNBUS-GW EtherCAT

Z9000010



Modular gateway EtherCAT, communication module for the base module RevPi Core / RevPi Core 3, a max. of two different communication modules can be connected, housing dimensions (H x W x D): 96 x 22.5 x 110.5 mm, protection type: IP 20, connection to the fieldbus: 2x RJ45, device function: Slave, max. data length input data: 512 Byte, max. data length output data: 512 Byte.

Technical details

General data

Approval: CE, UKCA

Technical data

Mechanical data

Height dimension:	96 mm
Width dimension:	22.5 mm
Depth dimension:	110.4 mm
Net weight:	91 g
Gross weight:	100 g

Environment

WEEE classification (08/2018): 5 devices (feed size < 50cm)

Commercial data

Harmonized System Code:	85389091
UNSPSC 25:	39122331
EAN-Code:	4046548093230
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27242290
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000024
ETIM Reference Feature:	EC001423

Volume:

0

Obligatory accessories



Z9000016

GW Connector for Modular Gateways