

KUNBUS-GW Ethernet/IP

Z9000009



Modular gateway Ethernet/IP, communication module for the base module RevPi Core / RevPi Core 3, a max. of two different communication modules can be connected, housing dimensions (H x W x D): 96 x 22.5 x 110.5 mm, protection type: IP 20, connection to the fieldbus: 2x RJ45, device function: Slave, max. data length input data: 480 Byte, max. data length output data: 480 Byte.

Technical details

General data	
Approval:	CE, UKCA
Technical data	
Mechanical data	
Height dimension:	96 mm
Width dimension:	22.5 mm
Depth dimension:	110.4 mm
Net weight:	95 g
Gross weight:	109 g
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85389091
UNSPSC 25:	39122331
EAN-Code:	4046548093223
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27242290
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000024
ETIM Reference Feature:	EC001423

Volume:

0

Obligatory accessories



Z9000016

GW Connector for Modular Gateways