

PNOZ mc1p

773700



PNOZmulti Classic, expansion module, standard, digital inputs and outputs, 16 outputs, semiconductors, 0.5 A, single-pole.

Technical details

General data

Approval: CE, UKCA, cULus Listed, KOSHA, EAC (Eurasian)

Technical data

Electrical data

Purpose of U2: Supply of SC outputs

Supply voltage 2 (V): 24 - 24 V

Type of supply voltage U2: DC

Potential isolation U2: Yes

Purpose of U1N1: Module supply

Source of internal voltage: Via base unit

Voltage type of U1N1: DC

Tolerance of U1N1. Module: -2 %/+2 %

Semiconductor outputs (standard)

Number of auxiliary outputs: 16

Galv. isol. n/safe SC O: Yes

Short circ. prot. n/safe S/C O: Yes

Signal level at 1 n/safe S/C O: UB - 0.5 VDC at 0.5 A

Environmental data

Ambient temperature standard: EN 60068-2-14

Ambient temperature: 0 - 0 °C

Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-30, EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
Condensation permitted?:	Not permitted
Perm. operating height ASL:	2000 m
EMC to standard ...:	EN 61131-2
Vibration to standard ...:	EN 60068-2-6
Acc. shock to standard1:	15g
Clearance & creepage dist. to:	EN 61131-2
Overvoltage category:	III
Pollution degree clear.&creep.:	2
Protection type standard:	EN 60529
Mechanical data	
Mounting position:	horizontal on top hat rail
DIN-rail dimensions:	35 x 7.5 EN 50022
Housing material lower section:	PPO UL 94 V0
Housing material front plate:	ABS UL 94 V0
Connection terminal:	Screw terminal, Spring-loaded terminal
Flex. cond. c/s AWG info:	24 - 16 AWG
Height dimension:	94 mm
Width dimension:	45 mm
Depth dimension:	121 mm
Net weight:	164 g
Gross weight:	182 g
Environment	
REACH compliance:	contains min. 1 SVHC-substance
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85389091

UNSPSC 25:	39122331
EAN-Code:	4046548012835
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27242208
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000024
ETIM Reference Feature:	EC001423
Volume:	0.695

Obligatory accessories

783700

PNOZ mc1p Set spring loaded terminals



793700

PNOZ mc1p Set plug in screw terminals



Optional accessories

774639

KOP-XE



779110

PNOZmulti Bus-Terminator

