

PMC output choke TEP3820-0CS41 17,5A

8C000100

Output choke TEP3820-0CS41 from a cable length > 50m, maximum of 100m
 Technical data: Voltage range 3x <480 VAC. Frequency range 0-200 Hz.
 Nominal current 17,5 A @ 4kHz / 15,2 A @ 8kHz. Inductance 0,9 mH.

Technical details

Technical data	
Electrical data	
Supply voltage with phases:	3 × 0 ... 480 VAC
Environmental data	
Ambient temperature:	0 - 40 °C
Mechanical data	
Height dimension:	153 mm
Width dimension:	178 mm
Depth dimension:	88 mm
Net weight:	5900 g
Gross weight:	5900 g
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85045000
UNSPSC 25:	39121012
EAN-Code:	4046548101072
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27420107
ETIM Version:	ETIM-9.0



THE SPIRIT OF SAFETY

ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC002563
Volume:	0