


PNOZ po3.3p 3n/o

773632



Expansion module PNOZpower modular safety system, 3 safety contacts (N/O) 5.5 kW (AC3 loads), plug-in terminals of screw type, width: 90 mm.

Technical details

General data

Approval: CCC, CE, UKCA, cULus Listed, EAC (Eurasian), TÜV

Technical data

Electrical data

Supply voltage (V): 24 - 24 V

Type of supply voltage U1: DC

Relay outputs

Utilisation cat. AC/DC1 stand.: EN 60947-4-1

Voltage AC1 safety cont.: 240 V

Max. current AC1 safety cont.: 16 A

Voltage DC1 safety cont.: 24 V

Max. current DC1 safety cont.: 16 A

Utilisation cat. AC15/DC13sta.: EN 60947-5-1

Voltage AC15 safety cont.: 230 V

Max. current AC15 safety cont.: 6 A

Voltage DC13 safety cont.: 24 V

Safety contacts: AC at UL: 240 VAC G. P.

Relay contact material: AgCdO

Environmental data

Climatic suitability to ...: EN 60068-2-78

Ambient temperature:	-10 - -10 °C
Humidity rating:	93 % r. h. at 40 °C
Condensation permitted?:	Not permitted
EMC to standard ...:	EN 60947-5-1, EN 61000-6-2, EN 61000-6-3, EN 61326-3-1
Vibration to standard ...:	EN 60068-2-6
Clearance & creepage dist. to:	EN 60947-1
Overvoltage category:	III
Pollution degree clear.&creep.:	2
Mechanical data	
Mounting position:	horizontal on top hat rail
Housing material upper part:	ABS UL 94 V0
Connection terminal:	Screw terminal
Terminal style:	plug-in
Flex. cond. c/s AWG info:	20 - 10 AWG
Height dimension:	94 mm
Width dimension:	90 mm
Depth dimension:	135 mm
Net weight:	625 g
Gross weight:	690 g
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85364900
UNSPSC 25:	39122331
EAN-Code:	4046548012873
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27371819
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000019



THE SPIRIT OF SAFETY

ETIM Reference Feature:	EC001449
Volume:	0.788