

PSEN me1.03M/AS n

570015



Mechanical safety guard locking device, with standard actuator, interlock principle magnetic force, contacts: 2 N/O, 2 N/C, supply voltage 24 V AC/DC, M12/5-pin connection.

Technical details

General data

Approval:	CE, BG, cCSAus, EAC (Eurasian)
unit type:	Unit

Technical data

Electrical data

Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	AC/DC

Relay outputs

Utilisation cat. AC15/DC13sta.:	EN 60947-5-1
---------------------------------	--------------

Environmental data

Mechanical data

Holding force:	1500 N
Connection type:	M12, 5-pin
Height dimension:	204.5 mm
Width dimension:	42.5 mm
Depth dimension:	51 mm
Net weight:	348 g
Gross weight:	440 g

Environment

RoHS directive:	2011/65/EU, 2015/863/EU
-----------------	-------------------------

RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	6c
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead, Butylphenol, Phenol
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1, 98-54-4, 84852-15-3
WEEE classification (08/2018):	5 devices (feed size < 50cm)
SCIP entry available:	yes
Commercial data	
Harmonized System Code:	85365080
UNSPSC 25:	39122205
EAN-Code:	4046548095418
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272603
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002593
Volume:	1.330

Optional accessories



380209

PSS67 Cable M12sf M12sm, 5m



630347

PSEN op cable angle M12 5-pole 3m

	570793	PSEN cable 200m-8x0.25mm²
	630348	PSEN op cable angle M12 5-pole 5m
	630349	PSEN op cable angle M12 5-pole 10m
	630350	PSEN op cable angle M12 5-pole 30m
	630298	PSEN cable M12-5sf 20m
	630310	PSEN op cable axial M12 5-pole 3m
	630297	PSEN op cable axial M12 5-pole 30m
	380220	PSS67 cable M12-5sf, M12-5sm, 20m
	380208	PSS67 Cable M12sf M12sm, 3m

	630311	PSEN op cable axial M12 5-pole 5m
	630312	PSEN op cable axial M12 5-pole 10m
	630364	PSEN op cable axial M12 5-pole 50m
	380210	PSS67 Cable M12sf M12sm, 10m
	630365	PSEN op cable angle M12 5-pole 50m
	380211	PSS67 Cable M12sf M12sm, 30m
	380214	PSS67 Cable M12af M12am, 10m
	380710	PDP67 Cable M12-5sf M12-5sm, 0.5m
	380215	PSS67 Cable M12af M12am, 30m



380212

PSS67 Cable M12af M12am, 3m



380213

PSS67 Cable M12af M12am, 5m



380713

PDP67 Cable M12-5sf M12-5sm, 2m



380711

PDP67 Cable M12-5sf M12-5sm, 1m



380712

PDP67 Cable M12-5sf M12-5sm, 1.5m