

MM A MINI-IO CAB99 1.5m

772200



Adapter cable for PNOZmulti 2 and PSS 4000 Motion Monitoring, 1.5 m.

Technical details

General data	
Approval:	-
Technical data	
Environmental data	
Ambient temperature:	0 - 0 °C
Condensation permitted?:	Not permitted
Mechanical data	
Connector type 1:	8-pin Mini-IO male connector
Shape of connector type 1:	straight
Contact surfaces material 1:	Au
Length cable:	1.5 m
Tolerance of cable length K1:	+/- 0.15 m
Colour cable insulation 1:	Green, similar to RAL6018
Material of cable insulation 1:	PUR
Trailing capability of cable 1:	yes
Bend radius (when laying) K1:	8 x Ø
Max. outside diameter cable K1:	6 - 6 mm
Conductor cross section:	0.14 - 0.14 mm²
Shielding K1:	yes
Number of conductors:	8

Approvals for cable K1:	UL AWM-Style 20233
Approvals for connector 1:	UL94 V-0
Net weight:	95 g
Gross weight:	105 g
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	6c
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1
WEEE classification (08/2018):	5 devices (feed size < 50cm)
SCIP entry available:	yes
Commercial data	
Harmonized System Code:	85444290
UNSPSC 25:	26121603
EAN-Code:	4046548079111
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27060313
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001855
Volume:	0