

PIT es Set3s-5ns

400454



PITestop, E-STOP/contact block incl. surface mount housing, set consisting of E-STOP pushbutton illuminated with E-STOP symbol and logo and contact block 2 N/C, with M12 connection 5-pin.

Technical details

General data

Approval:	CE
Self-monitored:	ja
Lamp:	LED
Lamp colour:	gelb

Technical data

Electrical data

Supply voltage (V):	12, 30
Type of supply voltage U1:	AC/DC
Min. contact current:	1

Emergency stop

Switch cap. E-STOP to standard:	EN 60947-5-1
Contact material E-STOP:	AgNi

Environmental data

Ambient temperature:	-25, 55
Pollution degree clear.&creep.:	3

Mechanical data

Mounting position:	any
Connection terminal:	M12
Height dimension:	103

Width dimension:	72
Depth dimension:	85
Diameter:	55
Net weight:	212
Gross weight:	250
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	6c
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1
WEEE classification (08/2018):	5 devices (feed size < 50cm)
SCIP entry available:	yes
Commercial data	
Harmonized System Code:	85371098
UNSPSC 25:	46171620
EAN-Code:	4046548071689
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27371244
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC002034
Volume:	0