

PIT si2.1 LED muting lamp

620015

PITsign LED muting lamp including LED and wall mounting, UB = 24 V DC / 4 W / <200 mA, protection type housing: IP65, diameter: 90 mm, height: 125 mm, signal lamp for muting mode.



Technical details

General data

Approval:	CE, UKCA
Self-monitored:	nein
Lamp:	LED
Lamp colour:	gelb

Technical data

Electrical data

Supply voltage (V):	24, 24
Type of supply voltage U1:	DC
Power consumption DC:	4

Environmental data

Ambient temperature:	-20, 50
----------------------	---------

Mechanical data

Cable entry:	ISO 20 mm
Mounting position:	upright
Housing material of cover:	PC
Housing material lower section:	ABS
Connection terminal:	Screw terminal
Height dimension:	125
Diameter:	90

Net weight:	205
Gross weight:	334
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85311095
UNSPSC 25:	39121534
EAN-Code:	4046548043723
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27143209
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000035
ETIM Reference Feature:	EC001332
Volume:	2.657