

PMC SC6A062Z/EC 2x 4,5A

8C000067



Technical data at 3 x 400 V AC: Nominal output current: 2x 4.5 A @ 4kHz / 2x 4.0 A @ 8kHz. I_{max}: 210% for 2s / 250% for 2s. Apparent power: 2x 3.1 KVA. Without brake resistor. Option: Without Safety module technology, with EtherCat.

Technische gegevens

Algemene data

Goedkeuring: UL Listed, CE, UKCA

Technische data

Elektrische data

Voedingsspanning met fasen: 3x400 VAC, +32/-50%, 50/60 Hz, 3x480 VAC, +10/-58%, 50/60 Hz

Voedingsspanning 2 (V): 24 - 24 V

Type voedingsspanning U2: DC

Ingangen

Milieugegevens

Omgevingstemperatuur: 0 - 45 °C

Type koeling: ingebouwde ventilator

Mechanische gegevens

Afmeting hoogte: 343 mm

Afmeting breedte: 45 mm

Afmeting diepte: 265 mm

Nettogewicht: 3650 g

Brutogewicht: 5250 g

Milieu

WEEE classificatie (08/2018): 5 devices (feed size < 50cm)

Commerciële gegevens

Harmonized System Code:	85044085
UNSPSC 25:	39121007
EAN-code:	4046548100877
ECLASS versie:	ECLASS-13
ECLASS reference feature:	27023101
ETIM versie:	ETIM-9.0
ETIM reference group:	EG000017
ETIM reference feature:	EC001857
Volume:	0

Verplichte Accessoires



8C000062

PMC SC6A062 terminal set (Y/Z)