

PMC PS6A24 25A/10KW

8C000001



Supply module for PMC SI6 drive controller. Technical data at 3 x 400 V AC: Nominal input current: 25 A. Maximum input current: 180% for 5s / 150% for 30s. Nominal power 10kW

Technische gegevens

Algemene data	
Goedkeuring:	UL Listed, CE, UKCA
Technische data	
Elektrische data	
Voedingsspanning met fasen:	3×400 VAC, +32/−50%, 50/60 Hz, 3×480 VAC, +10/−58%, 50/60 Hz
Voedingsspanning 2 (V):	24 - 24 V
Type voedingsspanning U2:	DC
Milieugegevens	
Omgevingstemperatuur:	0 - 45 °C
Type koeling:	ingebouwde ventilator
Mechanische gegevens	
Afmeting hoogte:	343 mm
Afmeting breedte:	45 mm
Afmeting diepte:	204 mm
Nettogewicht:	2680 g
Brutogewicht:	4180 g
Milieu	
WEEE classificatie (08/2018):	5 devices (feed size < 50cm)
Commerciële gegevens	
Harmonized System Code:	85044085

UNSPSC 25:	39121007
EAN-code:	4046548100112
ECLASS versie:	ECLASS-13
ECLASS reference feature:	27023101
ETIM versie:	ETIM-9.0
ETIM reference group:	EG000017
ETIM reference feature:	EC001857
Volume:	0

Verplichte Accessoires



8C000002

PMC PS6A24 terminal set