

PMC SI6A061Z/EC 1x 5A

8C000011



Technical data at 3 x 400 V AC: Nominal output current: 1x 5 A @ 4kHz / 1x 4.5 A @ 8kHz. I_{max}: 210% for 2s / 250% for 2s. Apparent power: 3.5 KVA. Without brake resistor. Option: Without Safety module technology, with EtherCat.

Technische gegevens

Algemene data	
Goedkeuring:	UL Listed, CE, UKCA
Technische data	
Elektrische data	
Voedingsspanning 2 (V):	24 - 24 V
Type voedingsspanning U2:	DC
Ingangen	
Milieugegevens	
Omgevingstemperatuur:	0 - 45 °C
Type koeling:	ingebouwde ventilator
Mechanische gegevens	
Afmeting hoogte:	343 mm
Afmeting breedte:	45 mm
Afmeting diepte:	265 mm
Nettogewicht:	3030 g
Brutogewicht:	4650 g
Milieu	
WEEE classificatie (08/2018):	5 devices (feed size < 50cm)
Commerciële gegevens	
Harmonized System Code:	85044085

UNSPSC 25:	39121007
EAN-code:	4046548100174
ECLASS versie:	ECLASS-13
ECLASS reference feature:	27023101
ETIM versie:	ETIM-9.0
ETIM reference group:	EG000017
ETIM reference feature:	EC001857
Volume:	0

Verplichte Accessoires



8C000006

PMC SI6A061 terminal set (Y/Z)