

PMC SI6A162R/EC 2x 12A

8C000031



Technical data at 3 x 400 V AC: Nominal output current: 2x 12 A @ 4kHz / 2x 10 A @ 8kHz. I_{max}: 210% for 2s / 250% for 2s. Apparent power: 2x 8.3 KVA. Without brake resistor. Option: Safety module SR6 (STO using terminals) and EtherCat.

Technische gegevens

Algemene data	
Goedkeuring:	UL Listed, CE, UKCA
Technische data	
Elektrische data	
Voedingsspanning 2 (V):	24 - 24 V
Type voedingsspanning U2:	DC
Ingangen	
Milieugegevens	
Omgevingstemperatuur:	0 - 45 °C
Type koeling:	ingebouwde ventilator
Mechanische gegevens	
Afmeting hoogte:	343 mm
Afmeting breedte:	65 mm
Afmeting diepte:	286 mm
Nettogewicht:	4870 g
Brutogewicht:	6290 g
Milieu	
WEEE classificatie (08/2018):	5 devices (feed size < 50cm)
Commerciële gegevens	
Harmonized System Code:	85044085

UNSPSC 25:	39121007
EAN-code:	4046548100310
ECLASS versie:	ECLASS-13
ECLASS reference feature:	27023101
ETIM versie:	ETIM-9.0
ETIM reference group:	EG000017
ETIM reference feature:	EC001857
Volume:	0

Verplichte Accessoires



8C000029

PMC SI6A162 terminal set (R)