PSEN sl-0.5 1.1 1actuator 570520



Actuator (standard), coded, for safety locking device PSENslock, aluminium base plate, for holding force 500 N

Technical details

General data	
Approval:	CE, UKCA, cULus Listed, FCC, IC, EAC (Eurasian), TÜV
Sensor principle:	Transponder
Coding level to ISO 14119:	Low
Transponder coding:	coded
unit type:	Actuator
Technical data	
Environmental data	
Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	-25 - 55 °C
EMC to standard ...:	EN 55011: Class A, EN 60947-5-3, EN 62061
Vibration to standard ...:	EN 60947-5-2
Acc. shock to standard1:	30g
Mechanical data	
Housing material upper part:	PBT
Material of anchor plate:	Nickel-plated steel
Material actuator:	Anticorodal, hard anodised
Height dimension:	138 mm
Width dimension:	52 mm
Depth dimension:	23 mm

Net weight:	375 g
Gross weight:	435 g
Environment	
WEEE classifikation (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85389099
EAN-Code:	4046548057324
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272606
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001487
Volume:	0

Optional accessories



540312 PSEN screw M5x20 10pcs



570550 PSEN sl bracket swing door



570551 PSEN sl bracket sliding door