

PSEN cs3.1 M12/8-1.5m/PSEN cs3.1 1unit

541014



RFID safety switch 2 safe SC outputs, 8-pin M12 male connector, with 1.5 m cable, one actuation direction, support for SDD IP6K9K, switching distance 11 mm, Sao = 8 mm, Sar = 20 mm, PU = 1 piece coded switch with actuator.

## Technical details

### General data

Approval:	CE, UKCA, cULus Listed, FCC, IC, TÜV, EAC (Eurasian)
Sensor principle:	Transponder
Coding level to ISO 14119:	Low
Classification to EN 60947-5-3:	PDDB
Transponder coding:	coded
Suitable for series connection:	yes
unit type:	Unit

### Technical data

#### Environment

RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	7a, 7c I
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead, Lead oxide
%-part of the pollutant:	> 0,1%
CAS No.:	7439-92-1, 1317-36-8
SCIP entry available:	yes
WEEE classification (08/2018):	5 devices (feed size < 50cm)

Commercial data	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27274601
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002592
UNSPSC 25:	39122205
GTIN:	4046548067231
Volume:	0 dm3
Harmonized System Code:	85365019
Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1

## Optional accessories



540324

PSEN cable angle M12 8-pole 10m



540325

PSEN cable angle M12 8-pole 30m



540326

PSEN cable axial M12 8-pole 30m



540338

PSEN Y junction M12-M12/M12 PIGTAIL



540320

PSEN cable axial M12 8-pole 5m



540342

PSEN cable M12-8sf M12-8sm, 10m



540331

PSEN T junction (auxiliary contact) M12



540321

PSEN cable axial M12 8-pole 10m



540343

PSEN cable M12-8sf M12-8sm, 20m



540322

PSEN cable angle M12 8-pole 3m



540344

PSEN cable M12-8sf M12-8sm, 30m



540333

PSEN cable M12-8sf, 20m



540323

PSEN cable angle M12 8-pole 5m



540319

PSEN cable axial M12 8-pole 3m

---



540130

SDD ES ETH

---



540340

PSEN cable M12-8sf M12-8sm, 2m

---



540341

PSEN cable M12-8sf M12-8sm, 5m

---



773603

PDP67 F 4 code

---