

PES sensor board enable-motor en

G9000006



Pilz Education System, modulopbygget kursussystem, betjeningspanelsensorteknologi III, med PITestop, PSENcode og PITenable, med nærhedsafbrydere til overvågning af DC-motorens omdrejningstal, betjeningspaneltekst på engelsk, medfølgende dokumenter på engelsk og tysk.

Tekniske data

Generelle data	
Godkendelse:	CE
Teknisk data	
Elektriske data	
Forsyningsspænding (V):	24 - 24 V
Forsyningsspændingstype U1:	DC
Miljøoplysninger	
Standard omgivelsestemperatur:	EN 60068-2-14
Omgivelsestemperatur:	0 - 0 °C
Standard opbevaringstemperatur:	EN 60068-2-30, EN 60068-2-78
Fugtbelastning oplysninger:	93 % RF ved 40 °C
Till. dr.højde over havoverfl.:	2000 m
EMC iht. standard:	EN 61131-2
Vibrationer iht. standard:	EN 60068-2-6
Accel. stød iht. stand. 1:	15g
Luft- og krybestrækninger iht.:	EN 61131-2
Mekaniske data	
Mål, højde:	399 mm
Mål, bredde:	297 mm
Mål, dybde:	200 mm

Nettovægt:	2600 g
Bruttovægt:	3100 g
Miljø	
WEEE klassifikation (08/2018):	5 devices (feed size < 50cm)
Kommercielle data	
Harmonized System Code:	90230080
UNSPSC 25:	46211501
EAN-kode:	4046548094183
ECLASS Version:	ECLASS-13
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000024
ETIM Reference Feature:	EC002584
Volumen:	53.596

Ekstra tilbehør



1S000004

PES test lead 4mm-rd



1S000005

PES test lead 4mm-bu



1S000003

PES test lead 4mm-bk



1S000008

PES test lead 4mm p-bu



1S000006

PES test lead 4mm p-bk



1S000007

PES test lead 4mm p-rd