

# UKCA-Declaration of Conformity

**PILZ**

original declaration

We **Pilz GmbH & Co. KG, Felix-Wankel-Str. 2, 73760 Ostfildern, Germany**

declare under our sole responsibility that the product

Safety laser scanner

Electro sensitive protective equipment (Type 3 ESPE)

product list see annex

complies with following UK legislation:

S.I. 2008/1597 Supply of Machinery (Safety) Regulations 2008

S.I. 2016/1093 Lifts Regulations 2016

S.I. 2016/1091 Electromagnetic Compatibility Regulations 2016

S.I. 2012/3032 The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012

Standards or technical rules applied for conformity assessment:

EN IEC 61496-1:2020, EN 61496-3: 2019, EN IEC 62061: 2021, EN ISO 13849-1: 2015  
EN 60825-1:2014+A11:2021, EN 61000-6-2: 2019

Consistency of a type sample with the legislation:

Supply of Machinery (Safety) Regulations 2008

has been certified by:

Notified body/ Address	TÜV Süd Product Service GmbH Ridlerstrasse 65 D-80339 München 0123
------------------------	---

Number of EC type examination certificate: M6A 020132-0282

Authorised representative

Pilz Automation Ltd, Pilz House, Little Colliers Field, Corby, Northants, NN18 8TJ, United Kingdom

<http://www.pilz.co.uk>

Signed for and on behalf of: Pilz GmbH & Co. KG

Ostfildern, 17.06.2025

Ort, Datum  
Place, Date

ppa. Holzäpfel, Matthias  
Vice President Product Development

Name, Vorname und Funktion des Unterzeichners  
surname, first name and function of signatory

Signed by:



874109681ACC440...  
Unterschrift  
signature

This declaration of conformity is suitable to the British Standard BS EN ISO/IEC 17050-1:2010: „Conformity assessment - Supplier's declaration of conformity - Part 1: General requirements“

UKCA Declaration Version 1.0, 2021-03

## Annex to UKCA - Declaration of conformity

product list

Safety laser scanner

Electro sensitive protective equipment (Type 3 ESPE)

PSEN scan – Autonomics:

PSEN sc B 5.5, range 5.5 m, light model

PSEN sc L 3.0 08-12, range 3 m, light model

PSEN sc L 5.5 08-12, range 5.5 m, light model

PSEN scan – Masters:

PSEN sc M 3.0 08-12, range 3 m, master model

PSEN sc M 5.5 08-12, range 5.5 m, master model

PSEN sc M 5.5 08-17, range 5.5 m, master model

PSEN sc ME 5.5 08-17, Encoder range 5.5 m, master model

PSEN sc PN 5.5 08 down, range 5.5m, PROFINET/PROFIsafe Master, Bottom Connector

PSEN sc PN 5.5 08 back, range 5.5m, PROFINET/PROFIsafe Master, Back Connector

PSEN scan – Slaves:

PSEN sc S 3.0 08-12, range 3 m, slave model

PSEN sc S 5.5 08-12, range 5.5 m, slave model

Accessories

memory-block

PSEN sc memory 08-12

PSEN sc memory 08-17

PSEN sc memory fbus (Exchangable memory-block fbus)