

PSEN cs3.1n 1switch

541053



RFID safety switch 2 safe SC outputs, 5-pin M12 male connector, one actuation direction, IP67, switching distance depends on actuator, PU = 1 piece coded switch (without actuator).

Technical details

General data

Approval:	CE, UKCA, cULus Listed, FCC, IC, TÜV, EAC (Eurasian)
Sensor principle:	Transponder
Coding level to ISO 14119:	Low
Classification to EN 60947-5-3:	PDDb
Transponder coding:	coded
Suitable for series connection:	no
unit type:	Sensor

Technical data

Electrical data

Supply voltage (V):	24, 24
Type of supply voltage U1:	DC
Power consumption DC:	1

Semiconductor outputs

Number of OSSD outputs:	2
Number of sig. outputs:	1
Potential isolation S/C O:	No
S/C output short circuit proof:	Yes
Utilisation cat. to EN 60947-1:	DC-12

Environmental data

Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	-25, 70
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
EMC to standard ...:	EN 60947-5-3
Vibration to standard ...:	EN 60947-5-2
Acc. shock to standard1:	30g
Overvoltage category:	III
Pollution degree clear.&creep.:	3
Switching distances	
Change op. distance temp.act.1:	+0.01mm/°C
Change op. distance temp.act.2:	+0.1mm/°C
Change op. distance temp.act.3:	+0.01mm/°C
Change op. distance temp.act.4:	+0.01mm/°C
Mechanical data	
Bend radius (when laying) K1:	5 x Ø
Sensor can be flush-mounted:	Yes, follow installation guide
Connection type:	M12, 5-pin male
Cable lines:	Li9Y11Y 8 x 0.14 mm ²
Housing material upper part:	PBT
Height dimension:	37
Width dimension:	26
Depth dimension:	18
Gross weight:	54
Transponder	
Operating frequency:	122 kHz - 128 kHz
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU

RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	7a, 7c I
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead, Lead oxide
%-part of the pollutant:	> 0,1%
CAS No.:	7439-92-1, 1317-36-8
WEEE classification (08/2018):	5 devices (feed size < 50cm)
SCIP entry available:	yes
Commercial data	
Harmonized System Code:	85365019
UNSPSC 25:	39122205
EAN-Code:	4046548060836
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27274601
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002592
Volume:	0

Obligatory accessories



541080

PSEN cs3.1 1 actuator



540080

PSEN cs1.1 1 actuator



541087

PSEN cs3.1 low profile glue 1 actuator



541088

PSEN cs3.1 low profile screw 1 actuator

Optional accessories



380209

PSS67 Cable M12sf M12sm, 5m



630347

PSEN op cable angle M12 5-pole 3m



630311

PSEN op cable axial M12 5-pole 5m



630312

PSEN op cable axial M12 5-pole 10m



630348

PSEN op cable angle M12 5-pole 5m



630349

PSEN op cable angle M12 5-pole 10m



630350

PSEN op cable angle M12 5-pole 30m



630298

PSEN cable M12-5sf 20m



380210

PSS67 Cable M12sf M12sm, 10m



630310

PSEN op cable axial M12 5-pole 3m



380211

PSS67 Cable M12sf M12sm, 30m



630297

PSEN op cable axial M12 5-pole 30m



380220

PSS67 cable M12-5sf, M12-5sm, 20m



380214

PSS67 Cable M12af M12am, 10m



380215

PSS67 Cable M12af M12am, 30m



773600

PDP67 F 8DI ION



380212

PSS67 Cable M12af M12am, 3m



380213

PSS67 Cable M12af M12am, 5m



380208

PSS67 Cable M12sf M12sm, 3m