

PZE X4V 2/24VDC 4n/o fix

774582



Contact expansion, inputs: 1-channel wiring, outputs: 4 N/O t-d, UB = 24 V DC, width: 22.5 mm, screw terminals integrated, delay-onde-energisation contact block for contact expansion in connection with safety-related control components, release time 2 s fixed.

Technical details

General data	
Approval:	CCC, CE, UKCA, cULus Listed, EAC (Eurasian), TÜV
Technical data	
Electrical data	
Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	DC
Power consumption DC:	2.5 W
Inputs	
Number of inputs:	1
Semiconductor outputs	
Number of semicond. outputs:	0
Relay outputs	
Utilisation cat. AC/DC1 stand.:	EN 60947-4-1
Utilisation cat. AC15/DC13sta.:	EN 60947-5-1
Safety contacts: AC at UL:	250 VAC G.U. (same polarity)
Safety contacts: pilot duty:	B300, R300
Relay contact material:	AgCuNi
Addit. contact details relay:	+ 0.2 µm Au
Environmental data	
Climatic suitability to ...:	EN 60068-2-78

Ambient temperature:	-10 - -10 °C
Humidity rating:	93 % r. h. at 40 °C
Condensation permitted?:	Not permitted
EMC to standard ...:	EN 60947-5-1, EN 61000-6-2, EN 61326-3-1
Vibration to standard ...:	EN 60068-2-6
Clearance & creepage dist. to:	EN 60947-1
Overvoltage category:	III / II
Pollution degree clear.&creep.:	2
Times	
Tolerance Tv:	-50 %/+50 %
Mechanical data	
Mounting position:	any
Housing material front plate:	ABS UL 94 V0
Connection terminal:	Screw terminal
Terminal style:	fixed
Flex. cond. c/s AWG info:	24 - 10 AWG
Height dimension:	87 mm
Width dimension:	22.5 mm
Depth dimension:	121 mm
Net weight:	205 g
Gross weight:	215 g
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85364900
UNSPSC 25:	39122331
EAN-Code:	4046548010800
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27371819

ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000019
ETIM Reference Feature:	EC001449
Volume:	0.284