

PNOZ s9 C 24VDC 3 n/o t 1 n/c t coated

751189



PNOZsigma timer relay (standalone), inputs: 1-channel wiring, outputs: 3 N/O t-d, 1 N/C, (t = 0.04 - 300 s), UB = 24 V DC, width: 17.5mm, plug-in spring-loaded terminals, contact block and timer relay for contact expansion in connection with safety-related control components or for the process of a safe timer function(energising, fallback, pulsing), coated version.

Technical details

General data	
Approval:	CCC, CE, UKCA, cULus Listed, KOSHA, EAC (Eurasian), TÜV
Technical data	
Electrical data	
Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	DC
Power consumption DC:	2 W
Relay outputs	
Number of del. aux. contacts:	1
Utilisation cat. AC/DC1 stand.:	EN 60947-4-1
Voltage AC1 safety cont.:	240 V
Max. current AC1 safety cont.:	6 A
Voltage DC1 safety cont.:	24 V
Max. current DC1 safety cont.:	6 A
Utilisation cat. AC15/DC13sta.:	EN 60947-5-1
Voltage AC15 safety cont.:	230 V
Max. current AC15 safety cont.:	5 A
Voltage DC13 safety cont.:	24 V
Safety contacts: AC at UL:	240 VAC G.U. (same polarity)
Relay contact material:	AgCuNi

Addit. contact details relay:	+ 0.2 µm Au
Environmental data	
Climatic suitability to ...:	EN 60068-2-78
Ambient temperature:	-10 - 55 °C
Humidity rating:	93 % r. h. at 40 °C
Condensation permitted?:	Not permitted
EMC to standard ...:	EN 60947-5-1, EN 61000-6-2, EN 61000-6-4, EN 61326-3-1
Vibration to standard ...:	EN 60068-2-6
Clearance & creepage dist. to:	EN 60947-1
Overvoltage category:	III
Pollution degree clear.&creep.:	2
Times	
Selectable times:	0.8 s, 0.7 s, 0.4 s, 0.2 s, 0.3 s, 15 s, 2.5 s, 1.5 s, 25 s, 35 s, 0.5 s, 0.6 s, 7 s, 6 s, 3 s, 5 s, 4 s, 210 s, 150 s, 0.1 s, 0.04 s, 8 s, 80 s, 90 s, 60 s, 50 s, 20 s, 40 s, 30 s, 16 s, 1 s, 2 s, 70 s, 100 s, 120 s, 140 s, 300 s, 200 s, 160 s, 3.5 s, 180 s, 14 s, 240 s, 12 s, 10 s
Tolerance Tv:	+/-1 % + +/-20 ms
Repetition accuracy:	+/-1 % + +/-20 ms
Tolerance in event of error:	+/-15 % + +/-20 ms
Min. delay time formula:	tv - 15 % - 20 ms
Max. delay time formula:	tv + 15 % + 20 ms
Mechanical data	
Mounting position:	any
Housing material lower section:	PC
Housing material front plate:	PC
Housing material upper part:	PC
Connection terminal:	Spring-loaded terminal
Terminal style:	plug-in
Height dimension:	100 mm
Width dimension:	17.5 mm

Depth dimension:	120 mm
Net weight:	175 g
Gross weight:	185 g
Environment	
REACH compliance:	contains min. 1 SVHC-substance
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85364900
UNSPSC 25:	39122331
EAN-Code:	4046548063073
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27371819
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000019
ETIM Reference Feature:	EC001449
Volume:	0.384

Optional accessories



750020

PNOZ s connector (10 pieces)



751003

PNOZ s Setspring loaded terminals 17,5mm