

PIT en1.0a-5m-s

401111

Enabling switch, 3 levels, 1 signal contact, 6-core cable (5 m) with open end.



Technical details

General data

Approval:	CE
Self-monitored:	nein

Technical data

Relay outputs

Utilisation cat. AC15/DC13sta.:	EN 60947-5-1
Voltage AC15 safety cont.:	125
Max. current AC15 safety cont.:	0.3
Voltage DC13 safety cont.:	30
Max.current DC12 safety cont.:	1

Environmental data

Ambient temperature:	0, 50
----------------------	-------

Mechanical data

Length cable:	5
Material of cable insulation 1:	PUR
Mounting position:	any
Connection type:	5m Kabel
Housing material lower section:	PP
Height dimension:	125
Width dimension:	45

Depth dimension:	45
Diameter:	45
Net weight:	361
Gross weight:	388
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	no
REACH compliance:	Contains no SVHC substances
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85371098
UNSPSC 25:	32131023
EAN-Code:	4046548065145
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27371238
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002571
Volume:	0