


Brake resistor 1600W/23R/T/U

8176334

suitable for the PMCprotego D/24A Type: FZZCQU 500 x 65-23
Performance at 40° C/100 % ED: 1600 W Resistance value: 23 OHM
Temperature switch 180° C: Signal contact 2A/24 V DC (DC11) UL version.



Technical details

General data	
Approval:	CE
Technical data	
Mechanical data	
Net weight:	5800 g
Gross weight:	6700 g
Environment	
WEEE classification (08/2018):	0 not relevant
Commercial data	
Harmonized System Code:	85333900
UNSPSC 25:	39121021
EAN-Code:	4046548065329
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27023291
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC002025
Volume:	0