

PNOZpe2p Bus-Interface

779125



Interface PNOZpower for externally connecting to PNOZsigma, PNOZ X, PNOZmulti, PNOZelog, PSS and SafetyBUSp.

Technical details

General data	
Approval:	CE, UKCA, cULus Listed, TÜV, EAC (Eurasian)
Technical data	
Electrical data	
Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	DC
Inputs	
Number of inputs:	1
Environmental data	
Climatic suitability to ...:	EN 60068-2-78
Ambient temperature:	-10 - -10 °C
Humidity rating:	93 % r. h. at 40 °C
Condensation permitted?:	Not permitted
EMC to standard ...:	EN 60947-5-1, EN 61000-6-2, EN 61326-3-1
Vibration to standard ...:	EN 60068-2-6
Clearance & creepage dist. to:	EN 60947-1
Overvoltage category:	III
Pollution degree clear.&creep.:	2
Mechanical data	
Mounting position:	horizontal on top hat rail

Connection terminal:	Screw terminal
Terminal style:	fixed
Flex. cond. c/s AWG info:	28 - 14 AWG
Height dimension:	29 mm
Width dimension:	23.5 mm
Depth dimension:	22.5 mm
Net weight:	15 g
Gross weight:	27 g
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85366990
UNSPSC 25:	39122331
EAN-Code:	4046548009088
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27379101
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC002498
Volume:	0.42