

## MM A MINI-IO CAB05 1.5m

772231



Motion Monitoring Adapter BOS/REX 15/15, 1.5 m.

### Technical details

| General data                  |                               |
|-------------------------------|-------------------------------|
| Approval:                     | cULus Listed                  |
| Technical data                |                               |
| Environmental data            |                               |
| Ambient temperature:          | 0 - 0 °C                      |
| Condensation permitted?:      | Not permitted                 |
| Mechanical data               |                               |
| Connector type 1:             | 15-pin D-Sub male connector   |
| Shape of connector type 1:    | straight                      |
| Connector type 2:             | 15-pin D-Sub female connector |
| Shape of connector type 2:    | straight                      |
| Connector type 3:             | 8-pin Mini-IO male connector  |
| Shape of connector type 3:    | straight                      |
| Fixing screws:                | UNC 4-40                      |
| Housing material connector 3: | PBT                           |
| Contact surfaces material 1:  | Au                            |
| Contact surfaces material 2:  | Au                            |
| Contact surfaces material 3:  | Au                            |
| Material of pins:             | Cu alloy                      |
| Material of sockets:          | Cu alloy                      |

|                                 |                              |
|---------------------------------|------------------------------|
| Length cable:                   | 1.5 m                        |
| Tolerance of cable length K1:   | +/- 0.15 m                   |
| Colour cable insulation 1:      | Green, similar to RAL6018    |
| Housing colour:                 | Black RAL 9005               |
| Material of cable insulation 1: | PUR                          |
| Trailing capability of cable 1: | yes                          |
| Bend radius (when laying) K1:   | 8 x Ø                        |
| Max. outside diameter cable K1: | 6 - 6 mm                     |
| Conductor cross section:        | 0.14 - 0.14 mm²              |
| Cable cross section AWG K1:     | 26                           |
| Shielding K1:                   | yes                          |
| Number of conductors:           | 8                            |
| Approvals for cable K1:         | UL AWM-Style 20233           |
| Approvals for connector 1:      | UL94 V-0                     |
| Approvals for connector 2:      | UL94 V-0                     |
| Approvals for connector 3:      | UL94 V-0                     |
| Housing material:               | TPE-SEBS UL 94 HB            |
| Height dimension:               | 38 mm                        |
| Width dimension:                | 40.8 mm                      |
| Depth dimension:                | 16 mm                        |
| Net weight:                     | 109 g                        |
| Gross weight:                   | 119 g                        |
| Environment                     |                              |
| WEEE klassifikation (08/2018):  | 5 devices (feed size < 50cm) |
| Commercial data                 |                              |
| Harmonized System Code:         | 85444290                     |
| UNSPSC 25:                      | 26121603                     |
| EAN-Code:                       | 4046548080582                |
| ECLASS version:                 | ECLASS-13                    |

|                           |          |
|---------------------------|----------|
| ECLASS Reference Feature: | 27060313 |
| ETIM Version:             | ETIM-9.0 |
| ETIM Reference Group:     | EG000026 |
| ETIM Reference Feature:   | EC001855 |
| Volume:                   | 0        |