

PMCcable FD/G4GB/010/Q25/S1

8C000110

Encoder cable for EnDat 2.1/2.2 digital. Cable assembled on both sides
Sub-connector <> con.17 round connector 12-pin. No. of wires and cross
section (3 x 2 x 0,14 mm² + 2 x 0,25 mm²). suitable for all PMC servo
controllers (SC6, SI6, SD6/X4) and the motors EZ40-EZ80. Length 10m.

Technical details

Technical data

Mechanical data

Connector type 1:	P 12-pin M17 female connector
Shape of connector type 1:	straight
Connector type 2:	15-pin D-Sub male connector
Shape of connector type 2:	straight
Contact surfaces material 1:	Au
Cable material K1:	Cu
Insulation material cable K1:	PP (9Y)
Length cable:	10 m
Material shield surface K1:	Cu tin-plated
Colour cable insulation 1:	Green
Material of cable insulation 1:	PUR
Trailing capability of cable 1:	yes
Bend radius (when laying) K1:	5 x Ø
Cross section data cable K1:	(3x2x0.14 + 2x0.25) mm ²
Shielding K1:	yes
Approvals for cable K1:	UL/CSA
Halogen-free:	yes
Oil resistance:	resistant

Flame resistance:	IEC 60332-1:self-extinguishing
Net weight:	720 g
Gross weight:	720 g
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85444290
UNSPSC 25:	26121603
EAN-Code:	4046548101560
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27060311
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001855
Volume:	0