


PNOZ m0p ETH

773113



Configurable safe small controllers PNOZmulti Classic, base unit, not expandable (link modules, 1 fieldbus module connectable), 2 Ethernet/Modbus TCP interfaces, 20 safe digital inputs, 4 safe semiconductor outputs, 2 safe relay outputs.

Technical details

General data

Approval: CE, UKCA, cULus Listed, KCC, KOSHA, EAC (Eurasian), TÜV

Technical data

Electrical data

Purpose of U1: System supply

Supply voltage (V): 24 - 24 V

Type of supply voltage U1: DC

Purpose of U2: Supply of SC outputs

Supply voltage 2 (V): 24 - 24 V

Type of supply voltage U2: DC

Potential isolation U2: Yes

Inputs

Max. no. live inputs: U_B ≤ 26.4 V : 20, U_B > 26.4 V : 15

Signal level at input at 0: -3 - +5 VDC

U input to EN 61131-2 Type 1: 24 V DC

Potential isolation input: No

Semiconductor outputs

Number of semicond. outputs: 4

Potential isolation of S/C O: Yes


S/C output short circuit proof: Yes

Semiconductor outputs (standard)	
Number of auxiliary outputs:	1
Galv. isol. n/safe SC O:	Yes
Short circ. prot. n/safe S/C O:	Yes
Signal level at 1 n/safe S/C O:	UB - 0.5 VDC at 0.5 A
Test clock outputs	
Number of test pulse outputs:	4
Relay outputs	
Number of relay outputs:	2
Utilisation cat. AC/DC1 stand.:	EN 60947-4-1
Voltage AC1 safety cont.:	240 V
Max. current AC1 safety cont.:	6 A
Voltage DC1 safety cont.:	24 V
Max. current DC1 safety cont.:	6 A
Utilisation cat. AC15/DC13sta.:	EN 60947-5-1
Voltage AC15 safety cont.:	230 V
Max. current AC15 safety cont.:	3 A
Voltage DC13 safety cont.:	24 V
Pot. isolation relay outputs:	Yes
Cascading output as standard output	
Number of cascading outputs:	1
Galv. isol. casc. aux. S/C O:	No
CANopen interface	
Number of Ethernet interfaces:	2
Environmental data	
Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	0 - 0 °C
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-30, EN 60068-2-78

Humidity rating:	93 % r. h. at 40 °C
Condensation permitted?:	Not permitted
Perm. operating height ASL:	2000 m
EMC to standard ...:	EN 61131-2
Vibration to standard ...:	EN 60068-2-6
Acc. shock to standard1:	15g
Clearance & creepage dist. to:	EN 61131-2
Overvoltage category:	III
Pollution degree clear.&creep.:	2
Protection type standard:	EN 60529
Potential separation	
Potential isolation 1 between:	SC output and system voltage
Type of potential isolation 1:	Safe separation
Potential isolation 2 between:	RL output and system voltage
Type of potential isolation 2:	Safe separation
Mechanical data	
Mounting position:	horizontal on top hat rail
DIN-rail dimensions:	35 x 7.5 EN 50022
Housing material lower section:	PPO UL 94 V0
Housing material front plate:	ABS UL 94 V0
Connection terminal:	Screw terminal, Spring-loaded terminal
Flex. cond. c/s AWG info:	24 - 16 AWG
Cond.flex AWG w/o crimp conn.:	24 - 12 AWG
Height dimension:	94 mm
Width dimension:	135 mm
Depth dimension:	121 mm
Net weight:	518 g
Gross weight:	537 g
Environment	

REACH compliance:	contains min. 1 SVHC-substance
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85371091
UNSPSC 25:	39122331
EAN-Code:	4046548066197
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27242207
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000024
ETIM Reference Feature:	EC000236
Volume:	1.680

Obligatory accessories



773010B

Basic Licence for PNOZmulti Config.



793100

PNOZ m1p/m0p plug in screw terminals




779211

Chipcard 1 piece 32kB



779201



PNOZmulti Chipcard 1 piece 8kb



783100

PNOZ m1p Set spring loaded terminals


Optional accessories

	779200	PNOZmulti Chipcard Set 10 piece 8KB
	773010L	Lite Licence for PNOZmulti Config.
	779212	PNOZmulti Chipcard Set 10 pieces 32kB
	779250	PNOZmulti Seal 12 pieces
	779240	PNOZmulti Chipcard Holder (Sparepart)
	779230	PNOZ Chip Card Reader
	779110	PNOZmulti Bus-Terminator
	779000	PNOZmulti Tool Kit
	773010V	User Upgr Licence for PNOZmulti Config




773011U

Basic Upgr Licence for PNOZmulti Service




773011V

User Upgr Licence for PNOZmulti Service




773010U

Basic Upgr Licence for PNOZmulti Config




773011B

Basic Licence for PNOZmulti Service




773011K

User Licence for PNOZmulti Service



773011L

Lite Licence for PNOZmulti Service



773010K

User Licence for PNOZmulti Config