



PSSu, electronic module, failsafe, supply voltage, infeed periphery supply 24 V DC 10 A, infeed C-rail 10 A.

Technical details

General data	
Approval:	CE, UKCA, cULus Listed, KOSHA, EAC (Eurasian), TÜV
Application range:	Standard/failsafe
Technical data	
Electrical data	
Purpose of U2:	Periphery supply
Supply voltage 2 (V):	24 - 24 V
Type of supply voltage U2:	DC
Tolerance of U2:	-30 %/+25 %
Potential isolation U1 to U2:	2500 V
Bridge U-interrupt UINT1 stan.:	EN 61131-2
Environmental data	
Climatic suitability to ...:	EN 60068-2-30, EN 60068-2-2, EN 60068-2-1, EN 60068-2-78, EN 60068-2-14
Ambient temperature:	0 - 60 °C
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
Condensation permitted?:	Not permitted
Perm. operating height ASL:	2000 m
EMC to standard ...:	EN 61131-2, EN 61000-6-2, EN 61000-6-4
Vibration to standard ...:	EN 60068-2-6

Acc. shock to standard1:	150 m/s ²
Clearance & creepage dist. to:	EN 61131-2
Overvoltage category:	II
Pollution degree clear.&creep.:	2
Protection type standard:	EN 60529
Mechanical data	
Housing material lower section:	PC
Housing material front plate:	PC
Housing material code:	PA
Terminal style:	plug-in
Height dimension:	76 mm
Width dimension:	12.6 mm
Depth dimension:	60.2 mm
Net weight:	33 g
Gross weight:	42 g
Name of coding element:	A
Colour of coding element:	Yellow
Environment	
WEEE klassifikation (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85044095
UNSPSC 25:	32131023
EAN-Code:	4046548018660
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27242611
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000024
ETIM Reference Feature:	EC002583
Volume:	0.049 dm ³

Obligatory accessories



312650

PSSu BS 1/8 S



312651

PSSu BS 1/8 C

Optional accessories



312900

PSSu A ET (10 pcs.)



312902

PSSu A EC



312901

PSSu A ETM (2 pcs.)



312967

PSSu A LA0.1 (10 x 108 pcs.)



312958

PSSu A LA0 (10 x 108 pcs.)



312949

PSSu A ET PE (10 pcs.)