

PDP67 cable M12-8sm, 10m

380702



Connection cable, PUR, yellow RAL1003, suitable for drag chains, 8-pin, connector straight M12, on open line end, A-coded, cable length: 10m

Technical details

General data

Approval: CE, UKCA, cULus Listed

Technical data

Electrical data

Rated current:	2 A
Typ. conductor resistance K1:	79 Ohm/km
Specific contact resistance K1:	$\geq 7E+15$ Ohm*cm
Specific conductor capacity K1:	64.6pF/m

Environmental data

Ambient temperature:	-25 - 80 °C
Pollution degree clear.&creep.:	3

Mechanical data

Connector type 1:	8-pin M12 male connector
Shape of connector type 1:	straight
Coding of M12 connector 1:	A coded
Contact surfaces material 1:	Au
Material of pins:	CuZn
Cable material K1:	Cu
Insulation material cable K1:	PP (9Y)
Cable type K1:	LiF9Y11Y

Length cable:	10 m
Colour cable insulation 1:	Yellow, similar to RAL 1003
Housing colour:	Black
Material of cable insulation 1:	TPU / TPE-U, PUR
Trailing capability of cable 1:	yes
Bend radius (when laying) K1:	5 x Ø
Max. outside diameter cable K1:	6.1 - 6.1 mm
Conductor cross section:	0.25 - 0.25 mm ²
Cable cross section AWG K1:	24
Stranding K1:	8 cores round plastic filler
Shielding K1:	no
Number of conductors:	8
Approvals for cable K1:	UL AWM-Style 20233, UL/CSA
Approvals for connector 1:	UL94 V-0
Halogen-free:	yes
Oil resistance:	resistant
Flame resistance:	UL VW1, FT1
Housing material:	PUR
Net weight:	554 g
Gross weight:	564 g
Environment	
WEEE klassifikation (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85444290
UNSPSC 25:	26121603
EAN-Code:	4046548065602
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27060311
ETIM Version:	ETIM-9.0

ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001855
Volume:	1.400 dm ³