

## P3WP3P C/5A/400VAC

490193



True power converter, measuring equipment for rated & absorbed true power, up to 3 motors/generators, measuring voltage 400 V AC, width width 90 mm, UB = 24 V DC.

## Technical details

General data	
Approval:	CE, UKCA
Technical data	
Electrical data	
Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	DC
Power consumption DC:	2.5 W
Max. device circuit breaker:	Max. conductor cross section
Measuring circuit	
U meas. range analogue input:	400 - 400 V
I meas. range analogue input:	0 - 6 A
Environmental data	
Climatic suitability to ...:	EN 60068-2-78
Ambient temperature:	0 - 60 °C
Condensation permitted?:	Not permitted
EMC to standard ...:	EN 61000-6-2, EN 61000-6-4
Vibration to standard ...:	EN 60068-2-6
Clearance & creepage dist. to:	EN 60947-1
Mechanical data	
Mounting position:	any

Housing material lower section:	PPO UL 94 V0
Housing material front plate:	ABS UL 94 V0
Connection terminal:	Spring-loaded terminal
Terminal style:	plug-in
Flex. cond. c/s AWG info:	22 - 12 AWG
Height dimension:	90 mm
Width dimension:	94 mm
Depth dimension:	121 mm
Net weight:	415 g
Gross weight:	470 g
<b>Environment</b>	
REACH compliance:	contains min. 1 SVHC-substance
WEEE classification (08/2018):	5 devices (feed size < 50cm)
<b>Commercial data</b>	
Harmonized System Code:	90303370
UNSPSC 25:	39122331
EAN-Code:	4046548064292
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27371806
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000019
ETIM Reference Feature:	EC001443
Volume:	1.296 dm <sup>3</sup>

## Optional accessories

490190

P3WP3P Set spring loaded terminals

