



Activatable Ethernet interfaces (RJ45), supply and input voltage 5 V

Technical details

General data

Approval: CE, UKCA, UL Recognized Component

Technical data

Electrical data

Supply voltage (V): 5 - 5 V

Type of supply voltage U1: DC

Power consumption DC: 0.3 W

Inputs

Number of inputs: 2

Galv. isolation input: No

Ethernet interface

Connector type ETHERNET int.: RJ45

Ethernet transmission rate: 10/100 Mbit/s

CANopen interface

Number of Ethernet interfaces: 2

Environmental data

Climatic suitability to ...: EN 60068-2-2

Ambient temperature: -20 - 60 °C

Climatic suitability standard: EN 60068-2-78

Humidity rating: 93 % r. h. at 40 °C

Condensation permitted?:	Not permitted
EMC to standard ...:	EN 61131-2 (Zone B)
Vibration to standard ...:	EN 60068-2-6
Clearance & creepage dist. to:	EN 61131-2
Overtoltage category:	II
Pollution degree clear.&creep.:	2
Mechanical data	
Mounting position:	any
Max. cable length:	30 m
Connection terminal:	Spring-loaded terminal, plugin
Height dimension:	40 mm
Width dimension:	30 mm
Depth dimension:	59.2 mm
Net weight:	42 g
Gross weight:	62 g
Environment	
WEEE classification (08/2018):	6 small IT-/communic. device
Commercial data	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27371292
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000017
ETIM Reference Feature:	EC002024

Optional accessories



402325

PIT or DIN rail adapter