

PSEN 2.1b-20/PSEN 2.1-20 /8mm/10m/1unit

502227



Magnetic safety switch 1 n/o 1 n/c, square design, IP6K9K, operating distance 8 mm, height design 13 mm, PU = 1 piece with actuator, with 10 m cable (PUR).

Technical details

General data	
Approval:	CE, UKCA, cULus Listed, EAC (Eurasian), ECOLAB, TÜV
Sensor principle:	magnetic
Coding level to ISO 14119:	Low
Classification to EN 60947-5-3:	PDDB
Suitable for series connection:	yes
unit type:	Unit
Technical data	
Electrical data	
Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	DC
Switching voltage:	24 V
Environmental data	
Ambient temperature:	-25 - 70 °C
Climatic suitability standard:	IEC 60068-2-30
Humidity rating:	93 % r. h. at 40 °C
Perm. operating height ASL:	2000 m
EMC to standard ...:	EN 60947-5-3
Vibration to standard ...:	EN 60947-5-2
Acc. shock to standard1:	30g

Pollution degree clear.&creep.:	3
Mechanical data	
Type 1 actuator:	PSEN 2.1-20
Sensor can be flush-mounted:	Ja, Montagehinweis beachten
Connection type:	10 m cable
Cable lines:	LiY11Y 4 x 0.25 mm ²
Housing material upper part:	PBT
Height dimension:	36 mm
Width dimension:	26 mm
Depth dimension:	13 mm
Net weight:	340 g
Gross weight:	357 g
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	no
REACH compliance:	Contains no SVHC substances
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85365019
UNSPSC 25:	39122205
EAN-Code:	4046548026733
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272402
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002544
Volume:	0 dm ³

Optional accessories



535110

PSEN i1 Interface for 4 PSEN 2



380308

PSS67 M12 connector, straight, male, 5pole



540310

PSEN screw M4x16 10pcs



380310

PSS67 M12 connector, angled, male, 5pole



534310

PSEN Distanzplatte / spacer (10 pcs.)



532110

PSEN Winkel / bracket



534320

PSEN reverse spacer