

PSEN 1.1a-20/PSEN 1.1-20 /8mm/5m/1unit

504226



Magnetic safety switch 2 n/o, square design, height design 13 mm, IP6K9K, switching distance 8 mm, PU = 1 piece with actuator, with 5 m cable (PUR).

Technical details

General data	
Approval:	CE, UKCA, cULus Listed, EAC (Eurasian), ECOLAB, TÜV
Sensor principle:	magnetic
Coding level to ISO 14119:	Low
Classification to EN 60947-5-3:	PDDB
Suitable for series connection:	no
unit type:	Unit
Technical data	
Electrical data	
Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	DC
Switching voltage:	24 V
Environmental data	
Ambient temperature:	-10 - 70 °C
Max. ambient temp. at 2000 m:	+70 °C
Climatic suitability standard:	IEC 60068-2-30
Humidity rating:	93 % r. h. at 40 °C
Perm. operating height ASL:	2000 m
EMC to standard ...:	EN 60947-5-3
Vibration to standard ...:	EN 60947-5-2

Acc. shock to standard1:	30g
Pollution degree clear.&creep.:	3
Mechanical data	
Type 1 actuator:	PSEN 1.1-20
Sensor can be flush-mounted:	Yes, follow installation guide
Connection type:	5 m cable
Cable lines:	LiY11Y 4 x 0.25 mm ²
Housing material upper part:	PBT
Height dimension:	36 mm
Width dimension:	26 mm
Depth dimension:	13 mm
Net weight:	167 g
Gross weight:	207 g
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	no
REACH compliance:	Contains no SVHC substances
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27274401
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002544
UNSPSC 25:	39122205
GTIN:	4046548026627
Volume:	0 dm ³
Harmonized System Code:	85365019

Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1

Optional accessories



380308

PSS67 M12 connector, straight, male, 5pole



540310

PSEN screw M4x16 10pcs



380310

PSS67 M12 connector, angled, male, 5pole



532110

PSEN Winkel / bracket



534310

PSEN Distanzplatte / spacer (10 pcs.)



534320

PSEN reverse spacer (2 pcs.)