

PSEN cs1.19n/PSEN cs1.19 1sw+OSSD1+OSSD2

540305

RFID safety switch, 2 safe SC outputs, 5-pin M12 male connector, 4 actuation directions, IP67, typ. operating distance 21 mm, Sao = 15 mm, Sar = 40 mm, PU = 1 piece coded switch with two actuators (OSSD1, OSSD2).



Technical details

General data	
Approval:	CE, UKCA, cULus Listed, FCC, IC, EAC (Eurasian), TÜV
Sensor principle:	Transponder
Coding level to ISO 14119:	Low
Classification to EN 60947-5-3:	PDDb
Transponder coding:	coded
Suitable for series connection:	no
unit type:	Unit
Technical data	
Electrical data	
Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	DC
Power consumption DC:	2 W
Semiconductor outputs	
Number of OSSD outputs:	2
Potential isolation S/C O:	No
S/C output short circuit proof:	Yes
Utilisation cat. to EN 60947-1:	DC-12
Environmental data	
Ambient temperature standard:	EN 60068-2-14

Ambient temperature:	-25 - 55 °C
Max. ambient temp. at 2000 m:	+55 °C
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
Perm. operating height ASL:	4000 m
EMC to standard ...:	EN 60947-5-3
Vibration to standard ...:	EN 60947-5-2
Acc. shock to standard1:	30g
Overvoltage category:	III
Pollution degree clear.&creep.:	3
Switching distances	
Change op. dist. temp.change:	+0.01mm/°C
Mechanical data	
Type 1 actuator:	PSEN cs1.19
Sensor can be flush-mounted:	Yes, follow installation guide
Connection type:	M12, 5-pin male
Housing material upper part:	PBT
Height dimension:	75 mm
Width dimension:	40 mm
Depth dimension:	40 mm
Net weight:	170 g
Gross weight:	216 g
Transponder	
Operating frequency:	122 kHz - 128 kHz
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes

RoHS except.s acc. to direct.:	7a, 7c I
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead, Lead oxide
%-part of the pollutant:	> 0,1%
CAS No.:	7439-92-1, 1317-36-8
SCIP entry available:	yes
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27274601
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002592
UNSPSC 25:	39122205
GTIN:	4046548071016
Volume:	0 dm3
Harmonized System Code:	85365019
Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1

Optional accessories



380209

PSS67 Cable M12sf M12sm, 5m



540311

PSEN screw M5x10 10pcs



540312

PSEN screw M5x20 10pcs



630347

PSEN op cable angle M12 5-pole 3m



630311

PSEN op cable axial M12 5-pole 5m



630312

PSEN op cable axial M12 5-pole 10m



630348

PSEN op cable angle M12 5-pole 5m



630349

PSEN op cable angle M12 5-pole 10m



630350

PSEN op cable angle M12 5-pole 30m












630298

PSEN cable M12-5sf 20m



380210

PSS67 Cable M12sf M12sm, 10m

	630310	PSEN op cable axial M12 5-pole 3m
	380211	PSS67 Cable M12sf M12sm, 30m
	380220	PSS67 cable M12-5sf, M12-5sm, 20m
	630297	PSEN op cable axial M12 5-pole 30m
	380214	PSS67 Cable M12af M12am, 10m
	380215	PSS67 Cable M12af M12am, 30m
	773600	PDP67 F 8DI ION
	380212	PSS67 Cable M12af M12am, 3m
	380213	PSS67 Cable M12af M12am, 5m



380208

PSS67 Cable M12sf M12sm, 3m
