

## PSEN T junction (auxiliary contact) M12

540331



Cable, Y-adapter- with T-plug-in connector, IP67, M12 male connector(X2, evaluation device), 8-pin, A-coded on M12 female connector (X1, sensor), 8-pin, A-coded and M8 female connector (X3, signal output /Lock\_Unlock), black, straight, 4-pin, A-coded, PUR, 0.25 m, 4× 0.25 mm<sup>2</sup>, black, to disconnect auxiliary signals when connecting PSENcode and PSENSlock.

## Technical details

General data	
Approval:	CE, UKCA
Technical data	
Electrical data	
Rated current:	2 A
Typ. conductor resistance K1:	58 Ohm/km
Specific contact resistance K1:	$\geq 1E+16$ Ohm*cm
Environmental data	
Ambient temperature:	-25 - 80 °C
Pollution degree clear.&creep.:	3
Mechanical data	
Connector type 1:	8-pin M12 female connector
Coding of M12 connector 1:	A coded
Connector type 2:	8-pin M12 male connector
Coding of M12 connector 2:	A coded
Connector type 3:	4 pin M8 male connector
Matl threaded ring conn 1:	GD-Zn, Ni
Matl threaded ring conn 2:	GD-Zn, Ni
Material threaded ring conn 3:	GD-Zn, Ni
Housing material connector 3:	PA

Contact surfaces material 1:	Ni, Au gal.
Contact surfaces material 2:	Ni, Au gal.
Contact surfaces material 3:	Ni, Au gal.
Seal material:	FPM
Material of pins:	CuZn
Material of sockets:	CuZn
Cable material K1:	Cu
Insulation material cable K1:	PP (9Y)
Cable type K1:	Li9Y11Y
Length cable:	0.25 m
Colour cable insulation 1:	Jet black RAL 9005
Housing colour:	Black
Material of cable insulation 1:	TPU / TPE-U
Bend radius (when laying) K1:	6 x Ø
Max. outside diameter cable K1:	4.55 - 4.55 mm
Conductor cross section:	0.25 - 0.25 mm <sup>2</sup>
Cable cross section AWG K1:	24
Stranding K1:	4 cores
Shielding K1:	no
Number of conductors:	4
Approvals for cable K1:	UL AWM-Style 20549
Approvals for connector 1:	UL 94
Approvals for connector 2:	UL 94
Approvals for connector 3:	UL 94
Halogen-free:	yes
Oil resistance:	resistant
Flame resistance:	cULus 20549
Housing material:	TPU, UL94
Net weight:	34 g

Gross weight:	42 g
<b>Environment</b>	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	6c
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1
SCIP entry available:	yes
WEEE classification (08/2018):	5 devices (feed size < 50cm)
<b>Commercial data</b>	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27274192
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002594
UNSPSC 25:	39122205
GTIN:	4046548062922
Volume:	0 dm3
Harmonized System Code:	85366990
Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1