

PSEN ml end adapter

570487



Plug-in connector, terminating adapter, IP67, M12 male connector (X2, evaluation device/previous plug-in connector), 8-pin, A-coded on M12 female connector (X3, sensor), 12-pin, A-coded, to terminate the series connection of PSENmlock.

Technical details

General data	
Approval:	CE, UKCA
Technical data	
Electrical data	
Rated current:	2 A
Environmental data	
Ambient temperature:	-20 - 80 °C
Pollution degree clear.&creep.:	3
Mechanical data	
Connector type 1:	12-pin M12 female connector
Coding of M12 connector 1:	A coded
Connector type 2:	8-pin M12 male connector
Coding of M12 connector 2:	A coded
Matl threaded ring conn 1:	Zn, nickel-plated
Matl threaded ring conn 2:	Zn, nickel-plated
Contact surfaces material 1:	Au
Contact surfaces material 2:	Au
Seal material:	FKM
Material of pins:	CuZn, gold-plated
Material of sockets:	CuZn, gold-plated

Housing colour:	Black
Housing material:	TPU
Net weight:	20 g
Gross weight:	21 g
Environment	
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272692
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002594
UNSPSC 25:	39122205
GTIN:	4046548088601
Volume:	0 dm3
Harmonized System Code:	85444290
Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1