



Safety locking device PSENslock, uniquely coded, with electromagnetic guard locking, with safety switch and actuator (standard), guard locking for process protection, holding force 1000 N, 8-pin M12 male connector, series connection

## Technical details

### General data

Approval:	CE, UKCA, cULus Listed, FCC, IC, EAC (Eurasian), TÜV
Sensor principle:	Transponder
Coding level to ISO 14119:	High
Classification to EN 60947-5-3:	PDDb
Transponder coding:	unique coding
Suitable for series connection:	yes
unit type:	Unit

### Technical data

#### Electrical data

Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	DC
Power consumption DC:	7.2 W

#### Inputs

Number of inputs:	3
DC voltage at input:	24 V DC

#### Semiconductor outputs

Number of OSSD outputs:	2
Number of sig. outputs:	1
S/C output short circuit proof:	Yes

Utilisation cat. to EN 60947-1:	DC-12
Environmental data	
Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	-25 - 55 °C
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
EMC to standard ...:	EN 55011: Class A, EN 60947-5-3, EN 62061
Vibration to standard ...:	EN 60947-5-2
Acc. shock to standard1:	30g
Overvoltage category:	III
Pollution degree clear.&creep.:	3
Mechanical data	
Holding force magnet on:	1000 N
Max. vertical offset:	5 mm
Max. angular offset:	2.5 deg
Type 1 actuator:	PSEN sl-1.0 2.1
Sensor can be flush-mounted:	Ja, Montagehinweis beachten
Connection type:	M12, 8-pin male
Cable lines:	LiYY 8 x 0.25 mm <sup>2</sup>
Housing material upper part:	PBT
Material of anchor plate:	Nickel-plated steel
Material of base plate:	Anticorodal, hard anodised
Material actuator:	Anticorodal, hard anodised
Height dimension:	172 mm
Width dimension:	45 mm
Depth dimension:	44 mm
Net weight:	1720 g
Gross weight:	1780 g

Transponder	
Operating frequency:	122 kHz - 128 kHz
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	7a, 6c, 7c I
REACH compliance:	Contains no SVHC substances
REACH included substances:	Lead, Lead oxide
%-part of the pollutant:	> 0,1%
CAS No.:	7439-92-1, 1317-36-8
WEEE classification (08/2018):	5 devices (feed size < 50cm)
SCIP entry available:	0
Commercial data	
Harmonized System Code:	85365019
UNSPSC 25:	39122205
EAN-Code:	4046548057409
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272603
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002593
Volume:	0 dm <sup>3</sup>

## Obligatory accessories



540324

PSEN cable angle M12 8-pole 10m



540325

PSEN cable angle M12 8-pole 30m



540326

PSEN cable axial M12 8-pole 30m



540320

PSEN cable axial M12 8-pole 5m



540321

PSEN cable axial M12 8-pole 10m



540322

PSEN cable angle M12 8-pole 3m



540323

PSEN cable angle M12 8-pole 5m



540319

PSEN cable axial M12 8-pole 3m

## Optional accessories



540342

PSEN cable M12-8sf M12-8sm, 10m



540331

PSEN T junction (auxiliary contact) M12



540343

PSEN cable M12-8sf M12-8sm, 20m



540333

PSEN cable M12-8sf, 20m



540344

PSEN cable M12-8sf M12-8sm, 30m



540312

PSEN screw M5x20 10pcs



570552

PSEN sl restart interlock (padlock)



570550

PSEN sl bracket swing door



540328

PSEN Y junction M12-M12/M12



570551

PSEN sl bracket sliding door



540340

PSEN cable M12-8sf M12-8sm, 2m

---



540341

PSEN cable M12-8sf M12-8sm, 5m

---



773603

PDP67 F 4 code

---