



Safety locking device PSENslock, uniquely coded, with electromagnetic guard locking, with safety switch and actuator (standard), guard locking for process protection, holding force 500 N, 8-pin M12 male connector, series connection Important information: This item is at the end of the product lifecycle and therefore will no longer be available in the foreseeable future. Please get in touch with your PILZ contact to find a suitable alternative or successor product.

## Technical details

General data	
Approval:	CE, UKCA, cULus Listed, FCC, IC, EAC (Eurasian), TÜV
Sensor principle:	Transponder
Coding level to ISO 14119:	High
Classification to EN 60947-5-3:	PDDb
Transponder coding:	unique coding
Suitable for series connection:	yes
unit type:	Unit
Technical data	
Electrical data	
Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	DC
Power consumption DC:	4.8 W
Inputs	
Number of inputs:	3
DC voltage at input:	24 V DC
Semiconductor outputs	
Number of OSSD outputs:	2
Number of sig. outputs:	1
S/C output short circuit proof:	Yes

Utilisation cat. to EN 60947-1:	DC-12
Environmental data	
Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	-25 - 55 °C
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
EMC to standard ...:	EN 55011: Class A, EN 60947-5-3, EN 62061
Vibration to standard ...:	EN 60947-5-2
Acc. shock to standard1:	30g
Overvoltage category:	III
Pollution degree clear.&creep.:	3
Mechanical data	
Holding force magnet on:	500 N
Max. vertical offset:	5 mm
Max. angular offset:	2.5 deg
Type 1 actuator:	PSEN sl-0.5 2.1
Sensor can be flush-mounted:	Yes, follow installation guide
Connection type:	M12, 8-pin male
Cable lines:	LiYY 8 x 0.25 mm <sup>2</sup>
Housing material upper part:	PBT
Material of anchor plate:	Nickel-plated steel
Material of base plate:	Anticorodal, hard anodised
Material actuator:	Anticorodal, hard anodised
Height dimension:	122 mm
Width dimension:	45 mm
Depth dimension:	44 mm
Net weight:	950 g
Gross weight:	990 g

Transponder	
Operating frequency:	122 kHz - 128 kHz
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	yes
RoHS except.s acc. to direct.:	7a
REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead
%-part of the pollutant:	> 0,1
CAS No.:	7439-92-1
SCIP entry available:	yes
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272603
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002593
UNSPSC 25:	39122205
GTIN:	4046548052282
Volume:	0 dm <sup>3</sup>
Harmonized System Code:	85365019
Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1

## Obligatory accessories



540324

PSEN cable angle M12 8-pole 10m



540325

PSEN cable angle M12 8-pole 30m



540326

PSEN cable axial M12 8-pole 30m



540320

PSEN cable axial M12 8-pole 5m



540321

PSEN cable axial M12 8-pole 10m



540322

PSEN cable angle M12 8-pole 3m



540323










PSEN cable angle M12 8-pole 5m



540319

PSEN cable axial M12 8-pole 3m

## Optional accessories

	540331	PSEN T junction (auxiliary contact) M12
	540342	PSEN cable M12-8sf M12-8sm, 10m
	540343	PSEN cable M12-8sf M12-8sm, 20m
	540333	PSEN cable M12-8sf, 20m
	540344	PSEN cable M12-8sf M12-8sm, 30m
	540312	PSEN screw M5x20 10pcs
	570552	PSEN sl restart interlock (padlock)
	540328	PSEN Y junction M12-M12/M12
	570550	PSEN sl bracket swing door



570551

PSEN sl bracket sliding door



540340

PSEN cable M12-8sf M12-8sm, 2m



540341

PSEN cable M12-8sf M12-8sm, 5m



773603

PDP67 F 4 code